



HSC12FR250, Heat Shrink Tubing PVC, Thin, FR, Clear

By Burndy
Catalog # [HSC12FR250](#)

.50" ID Min (Expanded), .25" ID Max (Recovered), Thin Wall, Fire Retardant, Clear, 250-Foot Reel



Features

- PVC Clear Heat Shrink Tubing
- #1-#4 Code, #4-#6 Flex
- 600 V, Fire Retardant

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	4AWG - 1AWG
Conductor Range	#6 AWG to #4 AWG

Configuration

Connector Type	CLEAR TUBES
----------------	-------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Length	3000 in
Height	0.5 in
Width	0.5 in
Dimensions	3000 in x 0.5 in x 0.5 in

General

Color	Clear
Trade Name	VISI-SHRINK™
Sub Brand	VISISHRINK
Product Type	PVC Thin Wall Heat Shrink
UPC	781810266182
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)