



HSC12T300PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC12T300PF](#)

.50" ID Min (Expanded), .25" ID Max (Recovered), Thin Wall, Clear, 25-Foot Reel

Features

- Heat Shrinkable Cross-Lined Thin Polyolefin Tube
- #6-#2 AWG, 600 V
- Shrink Ratio 2:1
- Standard Reel Size 25 Feet

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	6AWG - 2AWG
Conductor Range	#6 AWG to #2 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	7 in
Package Width	6 in
Package Weight	3.2 lb.
Package Height	7 in
Length	300 in
Width	0.5 in
Height	0.5 in
Dimensions	300 in x 0.5 in x 0.5 in

General

Sub Brand	VISISHRINK
Color	Clear
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810213803

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	630

Product Assets

[Catalog \[English\]](#)