



HSC12T48PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC12T48PF](#)

.50" ID Min (Expanded), .25" ID Max (Recovered), Thin Wall, Clear, 4-Foot Reel

Features

- Clear Heat Shrink Tubing
- .50" ID Min (Exp), .25" ID Max (Rec)
- #6-#2, Polyolefin, Thin Wall
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#6 AWG to #2 AWG
Conductor Size	6AWG - 2AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.5 in
Height	0.5 in
Length	48 in
Dimensions	48 in x 0.5 in x 0.5 in

General

Material	Cross-linked Polyolefin
UPC	781810212721
Color	Clear

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)