



HSC14FR, Heat Shrink Tubing PVC, Thin, Flame Rtrdnt, Clear

By Burndy
Catalog # [HSC14FR](#)



.25" ID Min (Expanded), .125" ID Max (Recovered), Flame Retardant, Clear, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	12AWG -8AWG
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	CLEAR TUBES
----------------	-------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Length	600 in
Height	0.25 in
Width	0.25 in
Dimensions	600 in x 0.25 in x 0.25 in

General

Color	Clear
Trade Name	VISI-SHRINK™
Sub Brand	VISISHRINK
Product Type	PVC Thin Wall Heat Shrink
UPC	781810266199
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	1
Pallet Quantity	256
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)