



HSC14FRFT, Heat Shrink Tubing PVC, Thin, Flame Rtrdnt, Clear

By Burndy
Catalog # [HSC14FRFT](#)



.25" ID Min (Expanded), .125" ID Max (Recovered), PVC, Flame Retardant, Clear, 50-Foot Reel

Features

- PVC Clear Heat Shrink Tubing
- #8-#12 Code, #10-#12 Flex
- 600 V, Fire Retardant

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.25 in
--------	---------

Width	0.25 in
Package Height	0.000 in
Length	600 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	600 in x 0.25 in x 0.25 in

General

Product Type	PVC Thin Wall Heat Shrink
UPC	781810033685

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[Catalog \[English\]](#)