



HSC14T300PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC14T300PF](#)

.25" ID Min (Expanded), .125" ID Max (Recovered), Flame Retardant, Clear, 25-Foot Reel

Features

- Heat Shrink Tubing
- 0.25" ID Min (Exp), 0.12" ID Max (Rec)
- #14-#10 AWG
- Cross Linked Polyolefin
- Thin Wall, Flame Retardant, Clear, 600 V

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	14AWG - 10AWG
Conductor Range	#14 AWG to #10 AWG

Configuration



Connector Type	THIN WALL REEL
Dimensions	
Package Length	7 in
Package Width	6 in
Package Weight	2.1 lb.
Package Height	7 in
Length	300 in
Width	0.25 in
Height	0.25 in
Dimensions	300 in x 0.25 in x 0.25 in

General

Sub Brand	VISISHRINK
Color	Clear
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810213605

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)