



HSC14T48PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC14T48PF](#)

.25" ID Min (Expanded), .125" ID Max (Recovered), Flame Retardant, Clear, 4-Foot Reel

Features

- Thin Wall Cross-Linked Clear Polyolefin Heat Shrink Tubing
- #10-#14 AWG, 600 V
- Flame Retardant

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	14AWG - 10AWG
Conductor Range	#14 AWG to #10 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	12.00 in
Package Width	21.00 in
Package Weight	0.66 lb.
Package Height	22.00 in
Length	48 in
Width	0.25 in
Height	0.25 in
Dimensions	48 in x 0.25 in x 0.25 in

General

Sub Brand	VISISHRINK
Color	Clear
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810212547

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)