



HSC150T48PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC150T48PF](#)

1.5" ID Min (Expanded), .75" ID Max (Recovered), Thin Wall, Clear,
4-Foot Reel

Features

- Clear Heat Shrink Tubing
- 1.5" ID Min (Exp), .75" ID Max (Rec)
- 2/O-350, Polyolefin, Thin Wall
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#2/O AWG - 350 Kcmil
Conductor Size	250kcmil - 500kcmil

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	1.5 in
Height	1.5 in
Length	48 in
Dimensions	48 in x 1.5 in x 1.5 in

General

Material	Cross-linked Polyolefin
UPC	781810212950
Color	Clear

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)