



HSC18FR, Heat Shrink Tubing PVC, Thin, Flame Rtrdnt, Clear

By Burndy
Catalog # [HSC18FR](#)



.125" ID Min (Expanded), .062" ID Max (Recovered), Thin Wall, Flame Retardant, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	16AWG - 14AWG
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type CLEAR TUBES

Dimensions

Length	600 in
Height	0.125 in
Width	0.125 in
Dimensions	600 in x 0.125 in x 0.125 in

General

Color	Clear
Trade Name	VISI-SHRINK™
Sub Brand	VISISHRINK
UPC	781810266212
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride

Logistics

Pallet Quantity	128
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)