



HSC18FR250, Heat Shrink Tubing PVC, Thin, FR, Clear

By Burndy
Catalog # [HSC18FR250](#)



.125" ID Min (Expanded), .062" ID Max (Recovered), Thin Wall, Flame Retardant, 250-Foot Reel

Features

- PVC Clear Heat Shrink Tubing
- #14-#16 Code and Flex
- 600 V
- Fire Retardant

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	16AWG - 14AWG
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type CLEAR TUBES

Dimensions

Length	3000 in
Height	0.125 in
Width	0.125 in
Dimensions	3000 in x 0.125 in x 0.125 in

General

Color	Clear
Trade Name	VISI-SHRINK™
Sub Brand	VISISHRINK
UPC	781810266229
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride

Logistics

Pallet Quantity	128
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)