



HSC18FR250FT, Heat Shrink Tubing PVC, Thin, FR, Clear

By Burndy
Catalog # [HSC18FR250FT](#)



.125" ID Min (Expanded), .062" ID Max (Recovered), PVC, Thin Wall, Flame Retardant, 250-Foot Reel

Features

- PVC Clear Heat Shrink Tubing
- #14-#16 Code and Flex
- 600 V
- Fire Retardant

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.125 in
Width	0.125 in
Package Height	0.000 in
Length	3000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	3000 in x 0.125 in x 0.125 in

General

Product Type	PVC Thin Wall Heat Shrink
UPC	781810038420

Logistics

Minimum Pack Quantity	250
-----------------------	-----

Product Assets

[Catalog \[English\]](#)