



HSC18T300PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC18T300PF](#)

.12" ID Min (Expanded), .06" Max (Recovered), Thin Wall, Clear,
25-Foot Reel

Features

- Heat Shrink Tubing, .12" Min (Exp), .06" ID Max (Rec)
- #18-#14 AWG, Cross Linked Polyolefin, Thin Wall
- Flame Retardant
- Clear
- 600 V

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	18AWG - 14AWG
----------------	---------------

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	7 in
Package Width	6 in
Package Weight	2.32 lb.
Package Height	7 in
Length	300 in
Width	0.125 in
Height	0.125 in
Dimensions	300 in x 0.125 in x 0.125 in

General

Sub Brand	VISISHRINK
Color	Clear
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810213469

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)