



HSC18T48PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC18T48PF](#)

.12" ID Min (Expanded), .06" Max (Recovered), Thin Wall, Clear, 4-Foot Reel

Features

- Thin Wall Cross-Linked Clear Polyolefin Heat Shrink Tubing
- #14-#18 AWG
- 600 V
- Flame Retardant

Application

For Terminations And Splices

Specifications

EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	18AWG - 14AWG
----------------	---------------

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	6 in
Package Width	1 in
Package Weight	0.56 lb.
Package Height	10 in
Length	48 in
Width	0.125 in
Height	0.125 in
Dimensions	48 in x 0.125 in x 0.125 in

General

Sub Brand	VISISHRINK
Color	Clear
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810212387

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)