



BURNDY

[HSC200FR100, Heat Shrink Tubing PVC, Thin, FR, Clear](#)

By Burndy

Catalog # [HSC200FR100](#)

2" ID Min (Expanded), 1" ID Max (Recovered), Thin Wall, Clear, 100-Foot Reel



Features

- Polyvinyl Chloride Clear Heat Shrink Tubing
- 800-1000 kcmil Code
- 500-750 kcmil Flex

Application

For Terminations And Splices

Specifications

Certification - ETL
No
Standards - RoHS Compliance Status
CM
EU RoHS Indicator
Yes
UL Listed
No
Certification - CSA Approved
Yes

Conductor

Conductor Size
800kcmil - 1000kcmil

Configuration

Connector Type
CLEAR TUBES

Dimensions

Length
1200 in
Height
2 in
Width
2 in
Dimensions
1200 in x 2 in x 2 in

General

Color
Clear
Trade Name
VISI-SHRINK™
Sub Brand
VISISHRINK
UPC
781810266243
Type
HSC-FR, Thin Wall, Flexible, Fire Retardant
Material
Polyvinyl chloride

Logistics

Pallet Quantity
360
Carton Quantity
1

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY_CA-HSC200FR100-SPEC-EN | REV 5/2026