



HSC316T300PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC316T300PF](#)

.19" ID Min (Expanded), .09" ID Max (Recovered), PVC, Clear, 25-Foot Reel

Features

- Thin Wall Cross-Linked Clear Polyolefin Heat Shrink Tubing
- #12-#18 AWG
- Flame Retardant

Application

For Terminations And Splices

Specifications

EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	18AWG - 12AWG
----------------	---------------

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	7.00 in
Package Width	6.00 in
Package Weight	2.23 lb.
Package Height	7.00 in
Length	300 in
Width	0.187 in
Height	0.187 in
Dimensions	300 in x 0.187 in x 0.187 in

General

Sub Brand	VISISHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810213537

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)