



HSC34FR, Heat Shrink Tubing PVC, Flame Rtrdnt, Clear

By Burndy
Catalog # [HSC34FR](#)

.75" ID Min (Expanded), .375" ID Max (Recovered), Flame Retardant, Clear, 50-Foot Reel



Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	1/0AWG - 3/0AWG
Conductor Range	#2 AWG to # 1/0 AWG

Configuration

Connector Type	CLEAR TUBES
----------------	-------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Length	600 in
Height	0.75 in
Width	0.75 in
Dimensions	600 in x 0.75 in x 0.75 in

General

Color	Clear
Trade Name	VISI-SHRINK™
Sub Brand	VISISHRINK
Product Type	PVC Thin Wall Heat Shrink
UPC	781810266250
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	1
Pallet Quantity	128
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)