



HSC34T1200PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC34T1200PF](#)

.75" ID Min (Expanded), .375" ID ID Max (Recovered), Flame Retardant, PVC, Clear, 100-Foot Reel

Features

- Clear Heat Shrink Tubing
- .75" ID Min (Exp), .38" ID Max (Rec)
- #1-3/0, Polyolefin, Thin Wall
- Shrink Ration 2:1
- 100 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Dimensions

Height	0.75 in
--------	---------

Width	0.75 in
Length	1200 in
Dimensions	1200 in x 0.75 in x 0.75 in

General

Color	Clear
UPC	781810271674
Material	Polyolefin

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)