



HSC34T300PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC34T300PF](#)

.75" ID Min (Expanded), .375" ID ID Max (Recovered), Flame Retardant, PVC, Clear, 25-Foot Reel

Features

- Clear Heat Shrink Tubing
- .75" ID Min (Exp), .38" ID Max (Rec)
- #1-3/0, Polyolefin, Thin Wall
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	1AWG - 3/0AWG
----------------	---------------

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	0.75 in
Width	0.75 in
Package Height	0.000 in
Length	300 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	300 in x 0.75 in x 0.75 in

General

Color	Clear
UPC	781810213889
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)