



HSC34T48PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC34T48PF](#)

.75" ID Min (Expanded), .375" ID ID Max (Recovered), Flame Retardant, PVC, Clear, 4-Foot Reel

Features

- Clear Heat Shrink Tubing
- .75" ID Min (Exp), .38" ID Max (Rec)
- #1-3/0, Polyolefin, Thin Wall
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	1AWG - 3/0AWG
----------------	---------------

Configuration

Connector Type	THIN WALL REEL
Dimensions	
Height	0.75 in
Width	0.75 in
Package Height	0.000 in
Length	48 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	48 in x 0.75 in x 0.75 in
General	
Color	Clear
UPC	781810212790
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)