



HSC38FR, Heat Shrink Tubing, Flame Retardant, Clear

By Burndy
Catalog # [HSC38FR](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), Flame Retardant, Clear, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	6AWG - 4AWG
Conductor Range	#8 AWG to #6 AWG

Configuration

Connector Type	CLEAR TUBES
----------------	-------------

Dimensions

Length	600 in
Height	0.375 in
Width	0.375 in
Dimensions	600 in x 0.375 in x 0.375 in

General

Color	Clear
Trade Name	VISI-SHRINK™
Sub Brand	VISISHRINK
UPC	781810266304
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride

Logistics

Pallet Quantity	1
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)



A Hubbell brand