



HSC38FR250, Heat Shrink Tubing, Thin Wall, FR, Clear

By Burndy
Catalog # [HSC38FR250](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), Flame Retardant, Clear, 250-Foot Reel

Features

- Clear Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, PVC, Fire Retardant
- Thin Wall, Shrink Ratio 2:1
- 50 Foot Reel

Application

Excellent flame retardant properties and a 2:1 shrink ratio. Tubing enables inspectors to read die index embossments on installed connectors easily

Specifications

Certification - CSA Approved	Yes
UL Listed	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG - 4AWG

Configuration

Connector Type	CLEAR TUBES
----------------	-------------

Dimensions

Width	0.375 in
Height	0.375 in
Length	3000 in
Dimensions	3000 in x 0.375 in x 0.375 in

General

Construction Material - Main	Polyvinyl Chloride
Sub Brand	VISI-SHRINK
Type	HSC-FR
Material	Polyvinyl chloride
UPC	781810266311
Trade Name	VISI-SHRINK™
Color	Clear

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)