



HSC38FR250FT, Heat Shrink Tubing PVC, Flame Retardant, Clear

By Burndy
Catalog # [HSC38FR250FT](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), PVC, Flame Retardant, Clear, 250-Foot Reel

Features

- Clear Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, PVC, Fire Retardant
- Thin Wall
- Shrink Ratio 2:1

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.375 in
Width	0.375 in
Package Height	0.000 in
Length	3000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	3000 in x 0.375 in x 0.375 in

General

Product Type	PVC Thin Wall Heat Shrink
UPC	781810038444

Logistics

Minimum Pack Quantity	250
-----------------------	-----

Product Assets

[Catalog \[English\]](#)