



HSC38FRFT, Heat Shrink Tubing PVC, Flame Retardant, Clear

By Burndy
Catalog # [HSC38FRFT](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), PVC, Flame Retardant, Clear, 50-Foot Reel

Features

- Clear Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, PVC, Fire Retardant, Thin Wall
- Shrink Ratio 2:1

Specifications

Buy American Compliant	Yes
Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2025) • Buy American Act Compliant (All status valid

- till December 2025)
- BABA Compliant (All status valid till December 2025)

Dimensions

Width	0.375 in
Height	0.375 in
Length	600 in
Dimensions	600 in x 0.375 in x 0.375 in

General

UPC	781810033692
-----	--------------

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[Catalog \[English\]](#)