



HSC38T300PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC38T300PF](#)

.38" ID Min (Expanded), .19" ID Max (Recovered), PVC, Flame Retardant, Clear, 25-Foot Reel

Features

- Clear Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	8AWG - 6AWG
Conductor Range	#8 AWG to #6 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	0.375 in
Width	0.375 in
Length	300 in
Dimensions	300 in x 0.375 in x 0.375 in

General

Color	Clear
UPC	781810213674
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)