



HSC38T48PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC38T48PF](#)

.38" ID Min (Expanded), .19" ID Max (Recovered), PVC, Flame Retardant, Clear, 4-Foot Reel

Features

- Clear Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

Configuration

Connector Type	THIN WALL REEL
Dimensions	
Width	0.375 in
Height	0.375 in
Length	48 in
Dimensions	48 in x 0.375 in x 0.375 in

General

Material	Cross-linked Polyolefin
UPC	781810212615
Color	Clear

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)