



HSG100T300PF, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSG100T300PF](#)

1" ID Min (Expanded), .50" ID Max (Recovered), Thin Wall, Fire Retardant, Green, 25-Foot Reel

Features

- Heat Shrink Tubing
- 1" ID Min (Exp), .5" ID Max (Rec)
- 2/0-300, Polyolefin, Thin Wall, Green
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#2/0 AWG - 300 Kcmil
Conductor Size	2/0AWG - 300kcmil

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	1 in
Height	1 in
Length	300 in
Dimensions	300 in x 1 in x 1 in

General

Material	Cross-linked Polyolefin
UPC	781810214015
Color	Green

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)