



HSG112FR, Heat Shrink Tubing, Thin Wall, FR, Green

By Burndy
Catalog # [HSG112FR](#)



1.5" ID Min (Expanded), .75" ID Max (Recovered), Fire Retardant, Thin Wall, Green, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	250-500 Kcmil
Conductor Size	350kcmil - 750kcmil

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	1.5 in
Height	1.5 in
Length	600 in
Dimensions	600 in x 1.5 in x 1.5 in

General

Material	Polyvinyl chloride
UPC	781810266342
Color	Green

Logistics

Minimum Pack Quantity	20
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)