



HSG116T300PF, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSG116T300PF](#)

.062" ID Min (Expanded), .032" Max (Recovered), Thin Wall, Green, 25-Foot Reel

Features

- Heat Shrink Tubing
- .062" ID Min (Exp), .032" ID Max (Rec)
- #18, Polyolefin, Thin Wall, Green
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	18AWG
Conductor Range	#18 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Length	300 in
Width	0.062 in
Height	0.062 in
Dimensions	300 in x 0.062 in x 0.062 in

General

Color	Green
Material	Cross-linked Polyolefin
UPC	781810213179

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	360

Product Assets

[Catalog \[English\]](#)