



HSG14FR250, Heat Shrink Tubing PVC, Thin Wall, FR, Green

By Burndy
Catalog # [HSG14FR250](#)



.25" ID Min Exp (Expanded), .13" ID Min Max (Recovered), Fire retardant, Thin Wall, Green, 250-Foot Reel

Features

- Heat Shrink Tubing
- .25" ID Min (Exp), .13" ID Max (Rec)
- #12-#10, PVC, Fire Retardant
- Thin Wall, Green
- 250 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	12AWG -8AWG
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Height	0.25 in
Width	0.25 in
Length	3000 in
Dimensions	3000 in x 0.25 in x 0.25 in

General

Color	Green
UPC	781810266397
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	40
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)