



HSG14T300PF, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSG14T300PF](#)

.25" ID Min Exp (Expanded), .13" ID Min Max (Recovered), Fire retardant, Thin Wall, Green, 25-Foot Reel

Features

- Heat Shrink Tubing
- .25" ID Min (Exp), .12" ID Max (Rec)
- #14-#10, Polyolefin, Thin Wall, Green
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	14AWG - 10AWG
Conductor Range	#14 AWG to #10 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	0.25 in
Width	0.25 in
Length	300 in
Dimensions	300 in x 0.25 in x 0.25 in

General

Color	Green
UPC	781810213636
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)