



HSG14T48PF, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSG14T48PF](#)

.25" ID Min Exp (Expanded), .13" ID Min Max (Recovered), Fire retardant, Thin Wall, Green, 4-Foot Reel

Features

- Heat Shrink Tubing
- .25" ID Min (Exp), .12" ID Max (Rec)
- #14-#10, Polyolefin, Thin Wall, Green
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	14AWG - 10AWG
Conductor Range	#14 AWG to #10 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Length	48 in
Width	0.25 in
Height	0.25 in
Dimensions	48 in x 0.25 in x 0.25 in

General

Color	Green
Material	Cross-linked Polyolefin
UPC	781810212578

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)