



HSG34T48PF, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSG34T48PF](#)

.75" ID Min (Expanded), .375" ID Max (Recovered), Thin Wall, Green, 4-Foot Reel

Features

- Heat Shrink Tubing
- .75" ID Min (Exp), .375" ID Max (Rec)
- #1-3/0, Polyolefin, Thin Wall, Green
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#1 AWG to #3/0 AWG
Conductor Size	1AWG - 3/0AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.75 in
Height	0.75 in
Length	48 in
Dimensions	48 in x 0.75 in x 0.75 in

General

Material	Cross-linked Polyolefin
UPC	781810212820
Color	Green

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)