



HSG38FR250, Heat Shrink Tubing PVC, Thin Wall, FR, Green

By Burndy
Catalog # [HSG38FR250](#)



.375" ID Min (Expanded), .19" ID Max (Recovered), PVC, Fire Retardant, Thin Wall, Green, 250-Foot Reel

Features

- Heat Shrink Tubing
- .375" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, PVC, Fire Retardant
- Thin Wall, Green
- 250 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG - 4AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.375 in
Height	0.375 in
Length	3000 in
Dimensions	3000 in x 0.375 in x 0.375 in

General

Material	Polyvinyl chloride
UPC	781810266472
Color	Green

Logistics

Minimum Pack Quantity	40
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)