



HSG38T48PF, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSG38T48PF](#)

.375" ID Min (Expanded), .19" ID Max (Recovered), Fire Retardant, Thin Wall, Green, 4-Foot Reel

Features

- Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall, Green
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	8AWG - 6AWG
Conductor Range	#8 AWG to #6 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	0.375 in
Width	0.375 in
Length	48 in
Dimensions	48 in x 0.375 in x 0.375 in

General

Color	Green
UPC	781810212653
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)