



HSIC350FR, Heat Shrink End Cap, Heavy Wall, Black

By Burndy
Catalog # [HSIC350FR](#)

2kV Rated, Fire Retardant, 3.5" ID Min (Expanded), 1.18" ID Max (Recovered), Thick Wall Heat Shrink End Cap, 4.5" Long, Black



Features

- Heavy Wall Cross Linked Polyolefin
- UV94-V0
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermochromic lines disappear during correct installation
- Rated up to 2kV
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor Size	1250kcmil
Conductor Range	1250 Kcmil

Configuration

Connector Type	HEAVY WALL END CAP
----------------	--------------------

Current

Voltage Rating	2000 V
----------------	--------

Dimensions

Height	3.5 in
Width	3.5 in
Package Height	0.000 in
Length	4.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	4.5 in x 3.5 in x 3.5 in

General

Product Type	Heavy Wall Black Polyolefin Heat Shrink End Cap
Color	Black
UPC	781810266571
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	7500
-----------------------	------

Product Assets

[Catalog \[English\]](#)