



HSIC81FREA, Heat Shrink End Cap, Heavy Wall, Black

By Burndy
Catalog # [HSIC81FREA](#)

2kV Rated, Fire Retardant, .5" ID Min (Expanded), .16" ID Max (Recovered), Thick Wall End Cap, 2.5" Long, Black



Features

- Heavy Wall Cross Linked Polyolefin
- UV94-V0
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermochromic lines disappear during correct installation
- Rated up to 2kV
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor Range	#4 AWG to #2/0 AWG
-----------------	--------------------

Dimensions

Package Height	0.000 in
Length	2.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	0.5 in
Width	0.5 in
Dimensions	2.5 in x 0.5 in x 0.5 in

General

Color	Black
UPC	781810083130
Material	Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	24000
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)