



HSM100T6PF7, Heat Shrink Tubing, Thin Wall, Mixed Colors Pkg

By Burndy
Catalog # [HSM100T6PF7](#)



1" ID Min (Expanded), .50" ID Max (Recovered), Thin Wall, 6" Lengths, Mixed Colors, 7 Pieces Total per package

Features

- Heat Shrink Tubing
- 1" ID Min (Exp), .5" ID Max (Rec)
- 2/0-300, Polyolefin, Thin Wall
- Multiple Color Package

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#2/0 AWG - 300 Kcmil
Conductor Size	2/0AWG - 300kcmil

Configuration

Connector TypeTHIN WALL TUBES

Dimensions

Width	1 in
Height	1 in
Length	6 in
Dimensions	6 in x 1 in x 1 in

General

Material	Cross-linked Polyolefin
UPC	781810214664
Color	Multiple Colors

Logistics

Minimum Pack Quantity	10
Carton Quantity	70

Product Assets

[Catalog \[English\]](#)