



HSM12T6PF10, Heat Shrink Tubing, Thin Wall, Mixed Colors Pkg

By Burndy
Catalog # [HSM12T6PF10](#)



.50" ID Min (Expanded), .03" ID Max (Recovered), Thin Wall, 6" Lengths, Mixed Colors, 10 Pieces Total per package

Features

- Heat Shrink Tubing
- .5" ID Min (Exp), .03" ID Max (Rec), #18
- Polyolefin, Thin Wall
- Multiple Color Package

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	6AWG - 2AWG
Conductor Range	#6 AWG to #2 AWG

Configuration

Connector Type	THIN WALL TUBES
----------------	-----------------

Dimensions

Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	0.5 in
Width	0.5 in
Dimensions	6 in x 0.5 in x 0.5 in

General

Color	Multiple Colors
UPC	781810214640
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1440
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)