



HSM14T6PF14, Heat Shrink Tubing, Thin Wall, Mixed Colors Pkg

By Burndy
Catalog # [HSM14T6PF14](#)



.25" ID Min (Expanded), .12" ID Max (Recovered), Thin Wall, 6" Lengths, Mixed Colors, 14 Pieces Total per package

Features

- Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing
- #10-#14 AWG, 600 V, 6" Length
- Flame Retardant
- Multiple Colors

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	14AWG - 10AWG
Conductor Range	#14 AWG to #10 AWG

Configuration

Connector Type	THIN WALL TUBES
----------------	-----------------

Dimensions

Package Height	10 in
Length	6 in
Package Weight	1 lb.
Package Length	6 in
Package Width	1 in
Height	0.25 in
Width	0.25 in
Dimensions	6 in x 0.25 in x 0.25 in

General

Color	Multiple Colors
Sub Brand	HEAT SHRINK
UPC	781810214626
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	10
Carton Quantity	140

Product Assets

[Catalog \[English\]](#)