



HSM18T6PF20, Heat Shrink Tubing, Thin Wall, Mixed Colors Pkg

By Burndy
Catalog # [HSM18T6PF20](#)



.12" ID Min (Expanded), .06" ID Max (Recovered), Thin Wall, 6" Lengths, Mixed Colors, 20 Pieces Total per package

Features

- Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing
- #14-#18 AWG, 600 V, 6" Length
- Flame Retardant
- Multiple Colors

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	18AWG - 14AWG
Conductor Range	#18 AWG to #14 AWG

Configuration

Connector Type	THIN WALL TUBES
----------------	-----------------

Dimensions

Package Length	6 in
Package Width	1 in
Package Weight	0.65 lb.
Package Height	10 in
Length	6 in
Width	0.125 in
Height	0.125 in
Dimensions	6 in x 0.125 in x 0.125 in

General

Sub Brand	HEAT SHRINK
Color	Multiple Colors
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810214589

Logistics

Minimum Pack Quantity	1
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)