



HSM34T6PF8, Heat Shrink Tubing, Thin Wall, Mixed Colors Pkg

By Burndy
Catalog # [HSM34T6PF8](#)



.75" ID Min (Expanded), .38" Max (Recovered), Thin Wall, 6" Lengths, Mixed Colors, 8 Pieces Total per package

Features

- Heat Shrink Tubing
- .75" ID Min (Exp), .375" ID Max (Rec)
- #1-3/0, Polyolefin, Thin Wall
- Multiple Color Package

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	1AWG - 3/0AWG
Conductor Range	#1 AWG to #3/0 AWG

Configuration

Connector Type	THIN WALL TUBES
----------------	-----------------

Dimensions

Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	0.75 in
Width	0.75 in
Dimensions	6 in x 0.75 in x 0.75 in

General

Color	Multiple Colors
UPC	781810214657
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	8
Pallet Quantity	1
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)