



HSM38T6PF12, Heat Shrink Tubing, Thin Wall, Mixed Colors Pkg

By Burndy
Catalog # [HSM38T6PF12](#)



.38" ID Min (Expanded), .19" Max (Recovered), Thin Wall, 6" Lengths, Mixed Colors, 12 Pieces Total per package

Features

- Heat Shrink Tubing
- .375" ID Min (Exp), .187" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall
- Multiple Color Package

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	8AWG - 6AWG
Conductor Range	#8 AWG to #6 AWG

Configuration

Connector Type	THIN WALL TUBES
----------------	-----------------

Dimensions

Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	0.375 in
Width	0.375 in
Dimensions	6 in x 0.375 in x 0.375 in

General

Color	Multiple Colors
UPC	781810214633
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1
Carton Quantity	120

Product Assets

[Catalog \[English\]](#)