



HSR100FR100, Heat Shrink Tubing PVC, Thin Wall, FR, Red

By Burndy
Catalog # [HSR100FR100](#)



1" ID Min (Expanded), .5" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 100-Foot Reel

Features

- Heat Shrink Tubing
- 1" ID Min (Exp), .5" ID Max (Rec)
- 1/0-4/0, PVC, Fire Retardant
- Thin Wall, Red
- 100 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#1/0 AWG to #4/0 AWG
Conductor Size	4/0AWG - 300kcmil

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	1 in
Height	1 in
Length	1200 in
Dimensions	1200 in x 1 in x 1 in

General

Material	Polyvinyl chloride
UPC	781810266618
Color	Red

Logistics

Minimum Pack Quantity	2
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)