



HSR100T48PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSR100T48PF](#)

1" ID Min (Expanded), .5" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 4-Foot Reel

Features

- Heat Shrink Tubing
- 1" ID Min (Exp), .5" ID Max (Rec)
- 2/0-300, Polyolefin, Thin Wall
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	2/0AWG - 300kcmil
Conductor Range	#2/0 AWG - 350 Kcmil

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	1 in
Width	1 in
Length	48 in
Dimensions	48 in x 1 in x 1 in

General

Color	Red
UPC	781810212875
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)