



HSR112FR100, Heat Shrink Tubing PVC, Thin Wall, FR, Red

By Burndy
Catalog # [HSR112FR100](#)



1.5" ID Min (Expanded), .75" ID Max (Recovered), Fire Retardant, Thin Wall, Red, 100-Foot Reel

Features

- Heat Shrink Tubing
- 1.5" ID Min (Exp), .75" ID Max (Rec)
- 250-500, PVC, Fire Retardant
- Thin Wall, Red
- 100 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	250-500 Kcmil
Conductor Size	350kcmil - 750kcmil

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	1.5 in
Height	1.5 in
Length	1200 in
Dimensions	1200 in x 1.5 in x 1.5 in

General

Material	Polyvinyl chloride
UPC	781810266632
Color	Red

Logistics

Minimum Pack Quantity	2
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)