



HSR116T48PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSR116T48PF](#)

.062" ID Min (Expanded), .032" ID Max (Recovered), Thin Wall,
Red, 4-Foot Reel

Features

- Heat Shrink Tubing
- .062" ID Min (Exp), .032" ID Max (Rec)
- #18, Polyolefin, Thin Wall, Red
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#18 AWG
Conductor Size	18AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.062 in
Height	0.062 in
Length	48 in
Dimensions	48 in x 0.062 in x 0.062 in

General

Material	Cross-linked Polyolefin
UPC	781810212240
Color	Red

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	4000

Product Assets

[Catalog \[English\]](#)