



HSR12FR, Heat Shrink Tubing PVC, Thin Wall, FR, Red

By Burndy
Catalog # [HSR12FR](#)



.5" ID Min (Expanded), .25" ID Max (Recovered), Fire Retardant, Thin Wall, Red, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#6 AWG to #4 AWG
Conductor Size	4AWG - 1AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.5 in
Height	0.5 in
Length	600 in
Dimensions	600 in x 0.5 in x 0.5 in

General

Material	Polyvinyl chloride
UPC	781810266649
Color	Red

Logistics

Minimum Pack Quantity	16
Carton Quantity	16
Pallet Quantity	128

Product Assets

[Catalog \[English\]](#)