



HSR12FRFT, Heat Shrink Tubing PVC, Thin Wall, FR, Red

By Burndy
Catalog # [HSR12FRFT](#)



.5" ID Min (Expanded), .25" ID Max (Recovered), PVC, Fire Retardant, Thin Wall, Red, 50-Foot Reel

Features

- Heat Shrink Tubing
- .5" ID Min (Exp), .25" ID Max (Rec)
- #6-#4, PVC, Fire Retardant
- Thin Wall, Red

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.5 in
Width	0.5 in
Package Height	0.000 in
Length	600 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	600 in x 0.5 in x 0.5 in

General

Product Type	PVC Thin Wall Heat Shrink
UPC	781810123515

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[Catalog \[English\]](#)