



# HSR12T300PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy  
Catalog # [HSR12T300PF](#)

.5" ID Min (Expanded), .25" ID Max (Recovered), Fire Retardant, Thin Wall, Red, 25-Foot Reel

## Features

- Heat Shrink Tubing
- .5" ID Min (Exp), .25" ID Max (Rec)
- Polyolefin, Thin Wall, Red, 600 V
- Shrink Ratio 2:1
- 25 Foot Reel

## Specifications

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| UL Listed                          | No  |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |

## Conductor

|                 |                  |
|-----------------|------------------|
| Conductor Range | #6 AWG to #2 AWG |
| Conductor Size  | 6AWG - 2AWG      |

## Configuration

|                |                |
|----------------|----------------|
| Connector Type | THIN WALL REEL |
|----------------|----------------|

## Dimensions

|            |                          |
|------------|--------------------------|
| Width      | 0.5 in                   |
| Height     | 0.5 in                   |
| Length     | 300 in                   |
| Dimensions | 300 in x 0.5 in x 0.5 in |

## General

|          |                         |
|----------|-------------------------|
| Material | Cross-linked Polyolefin |
| UPC      | 781810213810            |
| Color    | Red                     |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[Catalog \[English\]](#)