



HSR14FR, Heat Shrink Tubing PVC, Thin Wall, FR, Red

By Burndy
Catalog # [HSR14FR](#)



.25" ID Min (Expanded), .13" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	12AWG -8AWG
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Height	0.25 in
Width	0.25 in
Length	600 in
Dimensions	600 in x 0.25 in x 0.25 in

General

Color	Red
UPC	781810266663
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	48
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)